

Rittal – The System.

Faster – better – everywhere.



DK 7480.035

Energy-Box, 482.6 mm (19")

State: 05.09.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7480.035 - Energy-Box, 482.6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1 – 3 , maximum accommodation of 22 items of installed equipment.

Features

Model No.	DK 7480.035
Product description	Depth-variable top hat rail for installed equipment to DIN 43 880 in sizes 1 – 3, e.g. to accommodate flush-type socket outlets, circuit-breakers, etc., with cable clamping at the rear and one N and one PE rail each on an insulated base/plinth.
Colour	RAL 7035
Supply includes	Energy-Box with depth-variable top hat rail for installed equipment to DIN 43880, sizes 1 – 3, with brush strip for cable entry at the rear Plastic hood including extension cover (UL94-V0) 44 connection clamps, 4 mm ² 2 connection clamps, 16 mm ² 2 blanking covers 12 clips for strain relief of the connection cables Identification strips, self-adhesive
Max. pitch units @ 18 mm	22
Note	Individual population with circuit-breakers at the factory available on request.
Dimensions	Width: 482.6 mm Height: 132.5 mm Depth: 155 mm
Units	3 U
Packs of	1 pc(s).
Net weight	2.354
Gross weight	2.54
Customs tariff number	94032080
EAN	4028177166004

Features

E-Number Sweden	E7239593
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

Energy-Box, 3 U,
with adjustable top-hat rail for installed equipment as per
DIN 43880 in sizes 1 - 3. A cable clamp is integrated
in the box. One N and one PE rails are already fitted
on isolated bases. The plastic cover, which includes an
extension cover (UL 94-V0), can hold a maximum of 22 pieces of
installed equipment (width = 18 mm).

Supply includes:

1 pcs. Energy-Box with depth adjustable top hat rail for installation
equipment to DIN 43880, sizes 1-3, maximum 22 HP, including mounted N-
and PE-rail on isolated base.

Within a brush strip on the backside for cable entry

1 pcs. plastic hood incl. extension cover (UL-94-V0)

44 pcs. connection clamps, 4 mm²

2 pcs. connection clamps, 16 mm²

2 pcs. blanking cover

12 pcs. clips for cable strain relief

Identificationstrips, self-adhesive