

Rittal – The System.

Faster – better – everywhere.



DK 7507.712

Mounting angles, 482.6 mm (19")

State: 29.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7507.712 - Mounting angles, 482.6 mm (19") for FlatBox

L-shaped bracket as 2nd attachment level

Features

Model No.	DK 7507.712
Product description	L-shaped bracket as 2nd attachment level
Material	Sheet steel, spray-finished
Colour	RAL 7035
Supply includes	Assembly parts for fast, tool-free assembly
Units	12 U
Note	The 2nd attachment level should always be ordered in the same height as the basic enclosure Partial configuration is not possible
Packs of	2 pc(s).
Net weight	1 kg
Gross weight	1.18 kg
PCF per pack (cradle-to-gate)	4.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Mounting angles, 482.6 mm (19"), 12 U, For FlatBox

Tender text

Mounting angles for 482.6 mm (19") components

12 U

As second rear mounting level in the Rittal FlatBox enclosure system. The rear mounting angles are always to be installed at enclosure height, partial installation is not possible.

Material: Sheet steel, spray finished in RAL 7035

1 pack of 2