


Rittal – The System.

Faster – better – everywhere.



TS 7826.245

Roof plate for cable entry, two-piece

State: 27.06.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 7826.245 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



Features

Model No.	TS 7826.245
Product description	In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting.
Material	Sheet steel
Colour	RAL 7035
To fit	Width: 1,200 mm Depth: 400 mm
Packs of	1 pc(s).
Net weight	7.235
Gross weight	7.616
Customs tariff number	73269098
EAN	4028177402331
ETIM 9	EC000744
ECLASS 8.0	27182405

Tender text

DK-TS roof plate for cable entry

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x D): 1200 mm x 400 mm