

# Rittal – The System.

Faster – better – everywhere.



## DK 7826.768

### Roof plate, vented

State: 21.07.2025 (Source: [rittal.com/ua-en](https://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7826.768 - Roof plate, vented for TS, TS IT

In exchange for the standard roof, with and without cable entry.



## Features

|                       |  |
|-----------------------|--|
| Model No.             | DK 7826.768  |
| Design                | One-piece without cable entry  |
| Product description   | In exchange for the standard roof. 72 mm high roof plate, all-round vent slots, clamp strip for cable entry. The two-piece design with cable entry allows convenient retrofitting. |
| Material              | Sheet steel  |
| Colour                | RAL 7035   |
| To fit                | Enclosure type: TS<br>TS IT<br>Width: 600 mm<br>Depth: 800 mm  |
| Packs of              | 1 pc(s).   |
| Net weight            | 7.002  |
| Gross weight          | 7.37   |
| Customs tariff number | 73269098   |
| EAN                   | 4028177345591  |
| ETIM 9                | EC000744   |
| ECLASS 8.0            | 27182405   |

# Tender text

DK-TS vented roof plate, W x D = 600 x 800 mm

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x H x D): 600 mm x 0 mm x 800 mm