


Rittal – The System.

Faster – better – everywhere.



DK 7827.480

Depth stays for TS

State: 01.08.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.480 - Depth stays for TS for L-shaped mounting angles into TS, 482.6 mm (19")

Ensures optimum clearance at the sides for cable routing, depth-variable attachment is facilitated by the attachment slots.

Features

| | |
|-----------------------|---|
| Model No. | DK 7827.480 |
| Design | Installation position, centre |
| Product description | The installation brackets are screw-fastened to the enclosure frame in the enclosure width. The mounting angle is attached to the bracket at the top and bottom. For partial enclosure configuration, the installation brackets may be attached to the TS punched sections with mounting flanges 17 x 73 mm on the outer attachment level of the enclosure frame. |
| Benefits | The brackets ensure optimum clearance at the sides for cable routing Depth-variable attachment possible using the attachment slots Suitable for 482.6 mm (19") partial installation |
| Applications | For upgrading existing TS applications |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| To fit | Enclosure type: TS Width: 800 mm |
| Packs of | 2 pc(s). |
| Net weight | 3.38 |
| Gross weight | 3.6 |
| Customs tariff number | 73182900 |
| EAN | 4028177302631 |
| ETIM 9 | EC002625 |

Features

ECLASS 8.0

27189234

Tender text

19" TS 8 installation bracket, central installation position

Material: Sheet steel, zinc-plated, passivated