


# Rittal – The System.

Faster – better – everywhere.



## VX 8001.219 Gland plate

State: 26.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8001.219 - Gland plate for VX, VX IT, VX SE

For individual configuration of the floor space. Potential equalisation is provided via assembly components and earthing points.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | VX 8001.219  |
| Product description   | For individual configuration of the floor space. Potential equalisation is achieved via assembly components and earthing points.                   |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Supply includes       | Assembly parts   |
| Note                  | At least one sliding plate is required to fully seal a base opening. For two-door enclosures, one pack is sufficient for one half of the enclosure |
| Dimensions            | Width: 690 mm<br>Depth: 237.5 mm   |
| To fit                | Enclosure type: VX<br>VX IT<br>VX SE<br>CX one-piece console<br>CX pedestal<br>Width: = 800 mm   |
| Packs of              | 1 pc(s).   |
| Net weight            | 2 kg   |
| Gross weight          | 2.3 kg   |
| Customs tariff number | 94039910   |
| ETIM 9                | EC002620   |
| ECLASS 8.0            | 27189261   |
| Product description   | VX Gland plate, WD: 800x237,5 mm   |

# Approvals

---

Approvals

UL + C-UL (listed)