



Rittal – The System.

Faster – better – everywhere.



VX 8100.740

Punched section without mounting flange, 23 x 64 mm

State: 07.07.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8100.740 - Punched section without mounting flange, 23 x 64 mm for VX, VX SE

For variable, individual interior installation of the enclosure frame on the inner mounting level.



Features

| | |
|----------------------|---|
| Model No. | VX 8100.740 |
| Product description | For variable, individual interior installation of the enclosure frame on the inner mounting level. Mounted flush with enclosure frame The additional mounting brackets mean it can also be used with a pre-installed mounting plate, and is also prepared for cutting to any required length. |
| Benefits | System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | 2 punched sections without mounting flanges 4 mounting brackets Assembly parts |
| Installation options | In VX on the inner mounting level, on the VX enclosure section In the VX SE, on the vertical enclosure section in conjunction with the VX adaptor rail Between two punched sections on the inner mounting level |

Features

| | |
|-----------------------|---|
| To fit | Enclosure type: VX VX SE To fit width/depth: 400 mm |
| Packs of | 2 pc(s). |
| Net weight | 1 |
| Gross weight | 1.006 |
| Customs tariff number | 73269098 |
| EAN | 4028177924505 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |