


Rittal – The System.

Faster – better – everywhere.



TS 8104.235

Side panel, screw-fastened, sheet steel

State: 12.04.2026 (Source: [rittal.com/ua-en](https://www.rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8104.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8104.235
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface
Material	Sheet steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 7035
Supply includes	Assembly parts
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure Area available for population: External dimension – 100 mm
To fit	Enclosure type: TS TS IT Height: 2,000 mm Depth: 400 mm
IP protection category to IEC 60529	IP 55
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	19 kg
Gross weight	20 kg
Customs tariff number	94039910
ETIM 9	EC002524

Features

ECLASS 8.0	27182101
Product description	TS Side panel, screw-fastened, for TS, TS IT, for WD: 2000x400 mm, Sheet steel
