

Rittal – The System.

Faster – better – everywhere.



TS 8184.235

Side panel, screw-fastened, sheet steel

State: 10.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8184.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

| | |
|-------------------------------------|--|
| Model No. | TS 8184.235 |
| Benefits | Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure Area available for population: External dimension – 100 mm |
| To fit | Enclosure type: TS TS IT Height: 1,800 mm Depth: 400 mm |
| IP protection category to IEC 60529 | IP 55 |
| Basic material | Sheet steel |
| Packs of | 2 pc(s). |
| Net weight | 16.6 kg |
| Gross weight | 17.8 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002524 |

Features

| | |
|---------------------|--|
| ECLASS 8.0 | 27182101 |
| Product description | TS Side panel, screw-fastened, for TS, TS IT, for WD: 1800x400 mm, Sheet steel |

Approvals

| | |
|--------------|------------------------------|
| Explanations | Declaration of conformity UK |
|--------------|------------------------------|
