

# Rittal – The System.

Faster – better – everywhere.



## TS 8610.885 Glazed door

State: 06.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8610.885 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



## Features

Model No.	TS 8610.885
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Viewing door frame with safety glass Locking rod with double-bit insert 180° hinges (4)
Visible area	Viewing window width: 660 mm Viewing window height: 1,640 mm
Viewing window height	1,640 mm

# Features

Assembly instruction	Lock components are required when mounting instead of the rear panel
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: TS TS IT VX SE Width: = 800 mm Height: = 1,800 mm
Packs of	1 pc(s).
Net weight	14.77 kg
Gross weight	15.6 kg
Customs tariff number	76101000
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	TS Glazed door, for TS, TS IT, SE, for WH: 800x1800 mm