

**Rittal – The System.**

Faster – better – everywhere.



**TS 8612.020**

**TS punched section with mounting  
flange, 17 x 73 mm**

State: 21.04.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.020 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



## Features

|                      |  |
|----------------------|--|
| Model No.            | TS 8612.020  |
| Design               | for the inner mounting level   |
| Product description  | For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.  |
| Material             | Sheet steel  |
| Surface finish       | Zinc-plated  |
| Supply includes      | Assembly screws  |
| Length               | 1,190 mm   |
| Installation options | On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round<br>On the horizontal VX SE enclosure section, top in the depth<br>In TP via rail for interior installation: In the width, for inner mounting level<br>As a mounting kit for component shelves in TS, VX SE, simply locate and secure |
| Assembly instruction | The rail for internal mounting is required when installing in TP   |

# Features

|                       |   |
|-----------------------|---|
| To fit                | Enclosure type: VX SE<br>TP<br>PC<br>IW<br>Width/depth: 1,200 mm  |
| Packs of              | 4 pc(s).  |
| Net weight            | 5.2 kg  |
| Gross weight          | 5.3 kg  |
| Customs tariff number | 73269098  |
| ETIM 9                | EC002625  |
| ECLASS 8.0            | 27189234  |
| Product description   | TS punched section with mounting flange, 17 x 73 mm, for inner mounting level: for W/D: 1200 mm, L: 1190 mm |