Rittal - The System.

Faster - better - everywhere.





TS 8612.050

TS punched section with mounting flange, 17 x 73 mm

State: 09.12.2025 (Source: rittal.com/ua-en)




TS 8612.050 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.







2

Features

Model No.	TS 8612.050
	10 00 12.000
Design	For the inner mounting level and for mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	490 mm
To fit door width	600 mm
Installation options	On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round
	On the horizontal VX SE enclosure section, top in the depth
	In TP via rail for interior installation: In the width, for inner mounting level
	As a mounting kit for component shelves in TS, VX SE, simply locate and secure
Assembly instruction	The rail for internal mounting is required when installing in TP

© Rittal 2025

Features

To fit	Enclosure type: VX SE
	TP
	PC
	IW
	Width/depth: 500 mm
Packs of	4 pc(s).
Net weight	2.008
Gross weight	2.199
PCF per pack (cradle-to-gate)	8.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177212084
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3