

Rittal – The System.

Faster – better – everywhere.



TS 8612.650

TS punched sections without mounting flanges, 45 x 88 mm

State: 15.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.650 - TS punched sections without mounting flanges, 45 x 88 mm

Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

| | |
|-----------------------|---|
| Model No. | TS 8612.650 |
| Design | for the inner mounting level |
| Product description | Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The twin profile with 11 rows of holes offers numerous additional opportunities for interior installation. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Installation options | On the vertical and horizontal TS, VX SE enclosure section |
| To fit | Enclosure type: the inner mounting level Width/depth: 500 mm |
| Packs of | 2 pc(s). |
| Net weight | 2.6 kg |
| Gross weight | 2.611 kg |
| Customs tariff number | 73269098 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS TS punched section without mounting flange, 45 x 88 mm, for inner mounting level: for WD: 500 mm |
