

Rittal – The System.

Faster – better – everywhere.



TS 8612.760

TS punched rail 25 x 38 mm

State: 02.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.760 - TS punched rail 25 x 38 mm

For heavy installations, with attachment holes. Installation options on the vertical TS enclosure section.



Features

| | |
|-----------------------|---|
| Model No. | TS 8612.760 |
| Product description | For heavy installations, with attachment holes. |
| Material | Sheet steel, 3.0 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly screws |
| Installation options | On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm pitch pattern For the external mounting angle of support rails, system support rails, C rails 30/15, cable clamp rails (right angle section), own assemblies |
| Note | In conjunction with the snap-on nut, particularly well-suited for dynamic connections |
| To fit | Width/depth: 600 mm |
| Packs of | 2 pc(s). |
| Net weight | 1.648 kg |
| Gross weight | 1.96 kg |
| Customs tariff number | 73269098 |
| ECLASS 8.0 | 27189261 |

Features

Product description

TS Punched rail 25 x 38 mm, for WD: 600 mm