

Rittal – The System.

Faster – better – everywhere.



VX 8619.750

Punched section with mounting flange, 14 x 39 mm

State: 08.07.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.750 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

| | |
|---|---|
| Model No. | VX 8619.750 |
| Product description | For attaching cable ducts, cable conduit holders, equipment installed on the door, etc. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Distance between fixing points | 875 mm |
| To fit door width | 1,000 mm |
| VX SE installation options | In door width 900 mm |
| AX stainless steel installation options | In enclosure height 1000 mm |
| Assembly instruction | For installation in AX sheet steel, only in conjunction with rail for interior installation AX |
| Note | For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required |

Features

| | |
|-------------------------------|--|
| To fit | Enclosure type: VX SE AX stainless steel Suitable for width or height or depth: 1,000 mm |
| Packs of | 4 pc(s). |
| Net weight | 1.776 kg |
| Gross weight | 2.06 kg |
| PCF per pack (cradle-to-gate) | 13.6 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, with mounting flange 14 x 39 mm, for door width:1000 mm |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|