### Rittal – The System.

Faster – better – everywhere.





# TS 8800.570 Cable duct

State: 02.12.2025 (Source: rittal.com/ua-en)



#### TS 8800.570 - Cable duct for vertical TS section

For mounting on the vertical enclosure section, on two bayed enclosure sections in the vicinity of baying.







#### **Features**

Model No.	TS 8800.570
Design	Width 50 mm, for assembly on one vertical enclosure section in the area of the side panel.
Benefits	The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.  The nominal break points of the bars are also designed for combination with the cable ducts for mounting plates.  A further nominal break at the mounting plate height allows direct entry to the cable duct.
Material	Hard PVC Flame-resistant, self-extinguishing
Colour	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm
Slot width	4.5 mm
Note	Can be shortened for other enclosure sizes.

© Rittal 2025

#### **Features**

Dimensions	Width: 50 mm
	Height: 1,600 mm
	Depth: 80 mm
To fit	Enclosure type: TS
	VX SE
	PC
	IW
	Height: ≤ 1,800 mm
Operating temperature range	60 °C
Packs of	8 pc(s).
Net weight	8.968
Gross weight	9.44
Customs tariff number	39259020
EAN	4028177238015
ETIM 9	EC000012
ECLASS 8.0	27400703

## Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3