

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.560 OM adaptors

State: 29.06.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.560 - OM adaptors with spring terminals



## Features

Model No.	SV 9340.560
Design	with spring terminals
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 45 mm Height: 272 mm
Connection of round conductors	1.5 - 6 mm <sup>2</sup>
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 237 mm
Packs of	1 pc(s).

## Features

---

Net weight	0.28 kg
Gross weight	0.293 kg
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm <sup>2</sup> , WH: 45x272 mm, support frame, support rail TS 45D, TS 45D-V

## Approvals

---

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK