


# Rittal – The System.

Faster – better – everywhere.



## SV 9342.570 Connection bracket

State: 06.04.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.570 - Connection bracket for circuit-breaker component adaptors

Pre-assembled, laminated flat copper for connecting standard, commercially available circuit-breakers.



## Features

Model No.	SV 9342.570
Product description	Pre-assembled, laminated flat copper for connecting standard, commercially available moulded case circuit-breakers (MCCB).
Material	Electrolytic copper F20
Note	Universal application for switchgear with a dimensional difference between the mounting level and the upper edge of the contact level of $20 \pm 5$ mm.
To fit Model No.	9342.500 9342.510 9342.540 9342.550
Version – laminated flat copper	Number of lamina: 6 Membrane width: 9 mm Membrane thickness: 0.8 mm
To fit manufacturer (model)	ABB (T1, T1 UL, T2, T2 UL) Eaton (NZM1, NZM1 UL, BZM B1) Schneider Electric (NSC100, NSE75, NSE100)
Packs of	3 pc(s).
Net weight	0.096 kg

# Features

---

Gross weight	0.103 kg
Copper weight (kg per piece)	0.032
Customs tariff number	85446010
ETIM 9	EC002270
ECLASS 8.0	27409221
Product description	SV Connection bracket E-Cu, for circuit-breaker component adaptor, SV 9342500/510/540/550

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---