

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.035 Fuse holders

State: 22.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.035 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

## Features

Model No.	SV 9345.035
Design	For category J fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection for round conductor	AWG 1 - 14
Type of electrical connection	Box terminal
For fuse type (class)	J
Rated operating current max.	60 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports)
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Dimensions	Width: 120 mm Height: 118 mm
Connection of round conductors	2.5 - 50 mm <sup>2</sup>
To fit fuses	Diameter: 27 mm Length: 60 mm
Voltage range for indicator lights	110 - 600 V
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7

## Features

---

Number of poles	3-pole
Round conductor cross-section	2.5 - 50 mm <sup>2</sup>
Packs of	2 pc(s).
Net weight	1.24 kg
Gross weight	1.28 kg
Copper weight (kg per piece)	0.118
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuseholder, Class J, 60 A, 600 V, 3-pole, (60 mm)

## Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK