


Rittal – The System.

Faster – better – everywhere.



SV 9393.230

Connection module

State: 31.01.2026 (Source: rittal.com/ua-en)



SV 9393.230 - Connection module REM 800-CON

For connecting spatially remote measuring points.

Features

Model No.	SV 9393.230
Product description	For connecting spatially remote measuring points.
Supply includes	2 connection modules 2 bus connectors (left/right) 2 shield clamps 2 screw terminals 2 end brackets
Operating temperature range	-10 °C...55 °C
Storage temperature range	-25 °C...70 °C
Ambient humidity (non-condensing)	5...25 %
Contamination level	2
IP protection category to IEC 60529	IP 20
For mounting on support rails	Yes
Connection of round conductors, fine wire with wire end ferrule	0.2 - 1.5 mm ²
Connection of round conductors, fine wire without wire end ferrule	0.2 - 1.5 mm ²
Connection of round conductors, single-wire	0.2 - 1.5 mm ²
Connection of round conductors, multi-wire	0.2 - 1.5 mm ²
Connection for round conductor	AWG 16 - 24
Packs of	2 pc(s).
Net weight	0.36

Features

Gross weight	0.366
Customs tariff number	85389099
EAN	4028177984974

Approvals

Explanations	Declaration of conformity
--------------	---------------------------