

Rittal – The System.

Faster – better – everywhere.



SV 9616.000

Mini-PLS component adaptor

State: 03.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9616.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

Features

| | |
|------------------------------|--|
| Model No. | SV 9616.000 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Connection cables (AWG) | AWG 10 |
| Rated operating voltage | 690 V, 3~ |
| Rated current max. | 40 A |
| Dimensions | Width: 54 mm Height: 160 mm |
| Support rails Qty/height | 1 / 7.5 mm |
| To fit manufacturer (model) | Schneider Electric Siemens GV3 max. 40 A 3RV10 31 max. 40 A |
| Packs of | 1 pc(s). |
| Net weight | 0.27 kg |
| Gross weight | 0.32 kg |
| Copper weight (kg per piece) | 0.046 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Mini-PLS component adaptor, 40 A, 690 V, 3-pole, connection cable AWG 10, WH: 54x160 mm, support rail H: 7,5 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |
