

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.310 Component adaptor

State: 09.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.310 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

## Features

Model No.	SV 9635.310
Design	Basic
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 7035
Note	The technical data may vary for UL applications
Rated current max.	16 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Electrical ratings UL	Rated operating voltage (max.) UL: 600 V AC
Connection cables (AWG)	AWG 14
Length of connection cable	120 mm
Support rails Qty/height	1 / 10 mm
Support rail type	static
Dimensions	Width: 45 mm Height: 160 mm Depth: 34.5 mm
Packs of	4 pc(s).
Net weight	0.4 kg
Gross weight	0.426 kg
Copper weight (kg per piece)	0.024

# Features

---

Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor (Basic), 16 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 14 (L: 120 mm), WH: 45x160 mm

---

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---