


Rittal – The System.

Faster – better – everywhere.



SV 9666.440 Circuit-breaker module

State: 08.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.440 - Circuit-breaker module

For accommodating standard circuit-breakers up to 250 A or 630 A.

Features

Model No.	SV 9666.440
Product description	Suitable for accommodating standard moulded-case circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. Cover is prepared for a lead seal.
Material	Cover: Polystyrene Support rail: Sheet steel, zinc-plated
Colour	RAL 7035
Supply includes	Assembly parts
Dimensions	Width: 500 mm Height: 450 mm
Size	Width units (WU) @ 250 mm: 2 Height units (U) @ 150 mm: 3
To fit manufacturer (model)	ABB (T4, T5) Eaton (NZM3) Schneider Electric (NSX400, NSX630) Siemens (3RV1.6., 3RV1.7., VL400, VL630, VT3)
Packs of	1 pc(s).
Net weight	2.53 kg
Gross weight	2.54 kg
Customs tariff number	85365019
ETIM 9	EC001893
ECLASS 8.0	27400608
Product description	SV circuit-breaker module (ISV), 2 WU (500 mm), 3 U (450 mm)

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK