

Rittal – The System.

Faster – better – everywhere.



SV 9666.580

NH slimline fuse-switch-disconnector module

State: 03.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.580 - NH slimline fuse-switch-disconnector module

For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance).

Features

Model No.	SV 9666.580
Product description	For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance).
Material	Cover: Polystyrene Holder: Fibreglass-reinforced plastic
Colour	RAL 7035
Supply includes	Assembly parts
Note	In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules.
Dimensions	Width: 500 mm Height: 450 mm
Size	Width units (WU) @ 250 mm: 2 Height units (U) @ 150 mm: 3
For size	6 x Gr. 00
To fit Model No.	9346.020 9346.030
To fit busbars	40 x 10
Centre-to-centre spacing of busbars	100 mm
Packs of	1 pc(s).
Net weight	2.3 kg
Gross weight	2.5 kg

Features

Customs tariff number	85369095
ETIM 9	EC001893
ECLASS 8.0	27400608
Product description	SV NH fuse-switch disconnecter module (ISV), 2 WU (500 mm), 3 U (450 mm), for 6 x size 00, (SV 9346XXX, 100 mm)

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---