

Rittal – The System.

Faster – better – everywhere.



SV 9673.940

TS punched rail 17 x 17 mm

State: 18.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9673.940 - TS punched rail 17 x 17 mm for TS

For building an auxiliary construction for dividing the busbar space and for individual use as mounting frame for low and medium loads.



Features

Model No.	SV 9673.940
Design	For the outer mounting level
Product description	Mounting angle with TS pitch on three sides. Suitable for building an auxiliary construction for dividing the busbar space, for individual use as a mounting frame for low and medium loads, and fastening to the internal or external mounting level of the TS 8 enclosure.
Material	Sheet steel, 1.5 mm
Surface finish	Zinc-plated
Length	262.5 mm
To fit	Enclosure type: TS 8 Width: = 400 mm Depth: = 400 mm
Packs of	12 pc(s).
Net weight	1.2 kg
Gross weight	1.261 kg
Customs tariff number	73269098
ETIM 9	EC002525
ECLASS 8.0	27189234

Features

Product description

SV Punched rail 17x17 mm, L: 262,5 mm, for TS