

Rittal – The System.

Faster – better – everywhere.



SV 9676.730

Direct connection terminal

State: 13.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.730 - Direct connection terminal for round conductors

For the direct connection of round conductors 95 – 300 mm² (single-wire and multi-wire).

Features

Model No.	SV 9676.730
Product description	For connecting round conductors to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness.
Material	Connection clamp: Brass, tin-plated Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Assembly instruction	The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply. Busbar claw with threaded insert M10
Bars per conductor	2
Connection of round conductors	95 - 300 mm ²
Mounting dimensions	60 mm
Packs of	1 pc(s).
Net weight	0.32 kg
Gross weight	0.327 kg
Customs tariff number	85369010
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Direct connection terminal, round conductor connection 95-300 mm ² , (Flat-PLS 60/100), excluding screw

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK