



Rittal – The System.

Faster – better – everywhere.



SV 9676.982 Threaded bolts

State: 24.06.2025 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.982 - Threaded bolts for sliding blocks and sliding nuts

For attaching connection components such as ring terminals.

Features

Model No.	SV 9676.982
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly parts
To fit busbars	Maxi-PLS 60
Dimensions	Thread: M12 Thread length: 50 mm
Packs of	8 pc(s).
Net weight	0.4
Gross weight	0.478
Customs tariff number	73181535
EAN	4028177606920
ETIM 9	EC002349
ECLASS 8.0	23110302

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------