


Rittal – The System.

Faster – better – everywhere.



SV 9677.915 Connection block

State: 18.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.915 - Connection block

For connecting cables and laminated copper bars.

Features

| | |
|--------------------------------|---|
| Model No. | SV 9677.915 |
| Product description | For connecting cables and laminated copper bars. |
| Material | Sheet steel, zinc-plated E-Cu, tin-plated |
| Cable outlet | Top/bottom |
| Type of electrical connection | Box terminal |
| Rated current max. | 1,000 A |
| Dimensions | Width: 98 mm |
| Connection of round conductors | 185 - 300 mm ² |
| To fit busbars | Height: 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.2 kg |
| Gross weight | 1.35 kg |
| Copper weight (kg per piece) | 0.893 |
| PCF per pack (cradle-to-gate) | 5.1 kg CO ₂ eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 85369095 |
| ETIM 9 | EC002270 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Connection block, 1000 A, 690 V, 1-pole, cable outlet top/bottom, round conductor connection 185-300 mm ² |

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK