

Rittal – The System.

Faster – better – everywhere.



SV 9681.208

Perforated mounting strip

State: 02.06.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9681.208 - Perforated mounting strip for partial door

For retrospective external mounting on partial doors, with 25 mm hole pitch pattern for mounting individual items on the rear of doors such as cable ducts, conduit holders, etc.



Features

| | |
|---------------------------------------|---|
| Model No. | SV 9681.208 |
| Product description | For retrospective external mounting on partial doors. The perforated mounting strips have a 25 mm pitch pattern of holes and may be used for mounting individual accessories such as cable ducts, conduit holders etc. on the rear of the door. Hole diameter of perforated mounting strip: 4.5 mm. |
| Material | Sheet steel, 1 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Length | 598 mm |
| Dimensions | Length: 598 mm |
| To fit | Width: 800 mm |
| OUT_SUITABLE_FOR_PARTIAL_DOOR_HEIGHTS | 150 - 800 mm |
| Packs of | 10 pc(s). |
| Net weight | 1.9 kg |
| Gross weight | 1.914 kg |
| PCF per pack (cradle-to-gate) | 6.9 kg CO2 eq (Cat B) |

Features

| | |
|-----------------------|--|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000386 |
| ECLASS 8.0 | 27400501 |
| Product description | SV Perforated mounting strip, L: 598 mm, for partial door WH: 800x150-800 mm |

Approvals

| | |
|--------------|------------------------------|
| Explanations | Declaration of conformity UK |
|--------------|------------------------------|