

Rittal – The System.

Faster – better – everywhere.



SZ 9765.250 Ground plinth

State: 23.05.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 9765.250 - Ground plinth for multifunctional enclosures

Stainless steel ground plinth for multifunctional enclosures.

Features

Model No.	SZ 9765.250
Material	Stainless steel 1.4016 (AISI 430)
Surface finish	Enclosure: Powder-coated, UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Assembly parts
Dimensions	Width: 2,000 mm Height: 660 mm Depth: 500 mm
To fit	Enclosure type: MFG 18
Packs of	1 pc(s).
Net weight	55 kg
Gross weight	70 kg
Customs tariff number	94039910
ETIM 9	EC000721
Product description	Ground plinth for multifunctional enclosure MFG 18, for W: 2000 mm, D: 500 mm, stainless steel

Tender text

Ground Plinth for MFC 18

Plinth system for outdoor installation, consisting of Basic housing, and 4x base feet.

Housing and base feet made of 2 mm stainless steel 1.4016.

Completely powder coated in
RAL 7035 pure polyester.
Material: stainless steel 1.4016
Surface: powder coated in RAL 7035, pure polyester
Dimensions: WHT 2000x 600 x 500
Brand: Rittal
Type: ground base for MFC 18 or equivalent
Manufacturer: Rittal GmbH & Co. KG