


# Rittal – The System.

Faster – better – everywhere.



## AE 1031.500

## Compact enclosures AE

State: 25/08/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1031.500 - Compact enclosures AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base



## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | AE 1031.500   |
| Material                             | Enclosure: Sheet steel<br>Door: Sheet steel, all-round foamed-in PU seal  |
| Surface finish                       | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                               |
| Colour                               | RAL 7035  |
| Supply includes                      | Enclosure with hinged door(s), of all-round solid construction<br>Gland plate(s) in enclosure base<br>Mounting plate<br>Lock: 3 mm double-bit |
| Protection category NEMA             | NEMA 4  |
| Protection category to IEC 60 529    | IP 66   |
| IK Code                              | IK08  |
| Dimensions                           | Width: 380 mm<br>Height: 300 mm<br>Depth: 210 mm  |
| Material thickness - door            | 1.5 mm  |
| Material thickness - enclosure       | 1.38 mm   |
| Material thickness of mounting plate | 2 mm  |

# Features

|                                   |   |
|-----------------------------------|---|
| Dimensions mounting plate (W x H) | 334 mm x 275 mm   |
| Number of doors                   | 1   |
| Interchangeable door hinge        | Yes   |
| Number of locks                   | 1   |
| Lock                              | Lock version: Cam<br>Number of locks: 1<br>Lock insert: 3 mm double-bit |
| Gland plate                       | Size: 3<br>Qty.: 1  |
| Basic material                    | Sheet steel   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 7.757   |
| Gross weight                      | 8.16  |
| Customs tariff number             | 94032080  |
| EAN                               | 4028177251984   |
| E-Number Sweden                   | E3404603  |
| ECLASS 8.0                        | 27180101  |

# Approvals

|              |   |
|--------------|---|
| Approvals    | Lloyds Register of Shipping<br>UL + C-UL (listed)         |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

Enclosure (compact enclosure); protection category IP 66

## Enclosure:

Robust steel sheet construction made from 1.25 mm or 1.5 mm steel sheet, folded and welded from a single piece, with protection channel around the door opening, rear panel with countersunk holes for wall mounting brackets. Enclosure base fitted with sheet steel gland plates.

## Doors:

1.5 mm - 2 mm sheet steel, flush-mounted, with foamed-in seal, vertical perforated mounting strips fitted on both sides, screw-fastened hinges. Hinges can be fitted on the left or right for single-door enclosures, 130° opening angle as per VDI (retrofitable to 180°), cam lock with double-bit insert as per DIN 43668

## Mounting plate:

2 - 3 mm sheet steel with system punchings, depth-adjustable stud mountings, zinc-plated.

## Accessories:

Lock inserts, wall mounting brackets, plastic gland plate, earthing straps, wiring plan pockets, door stay, viewing window, panels, heat exchanger, fan-and-filter units, heaters, swing frame, electronic accessories (for 600 mm wide enclosures only), rain canopy, 180° hinge

## Surface finish:

Panels cleaned, degreased, phosphated, electrophoretic dipcoat primed and powder-coated with polyester powder in textured RAL 7035.

Dimensions (W x H x D): 380 x 300 x 210 mm