

# Rittal – The System.

Faster – better – everywhere.



## EL 2092.300 Captive nuts

State: 05/08/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# EL 2092.300 - Captive nuts

M5/M6, for the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19").

## Features

Model No.	EL 2092.300
Design	without contact
Product description	For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure.
Dimensions	Thread: M6
For material thicknesses	1.2 - 1.5 mm
Packs of	50 pc(s).
Net weight	0.15
Gross weight	0.202
Customs tariff number	73181692
EAN	4028177187382
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815