Rittal – The System.

Faster – better – everywhere.





AX 2571.100 Metal gland plate

State: 29/10/2025 (Source: rittal.com/uae-en)



AX 2571.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

AX 2571.100
Simply knock out the holes for the cable glands using a screwdriver
Sheet steel
RAL 7035
The allocation of gland plate sizes is indicated on the relevant enclosures
2 x M12 2 x M16 9 x M20
5 x M25 1 x M32 1 x M40
Width: 256 mm Depth: 149 mm
Enclosure type: AX
Size: 1
IP 66 if installed correctly
Type 1 Type 12K
2 2 9 5

© Rittal 2025

Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packs of	1 pc(s).
Net weight	0.46
Gross weight	0.469
PCF per pack (cradle-to-gate)	2.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73079100
EAN	4028177925304
E-Number Sweden	E3465295
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3