

# Rittal – The System.

Faster – better – everywhere.



## FT 2796.000 Acrylic glazed cover

State: 22/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2796.000 - Acrylic glazed cover

For the protection of display and control components in standard 482.6 mm (19") or metric sizes.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | FT 2796.000   |
| Design                            | 482.6 mm (19")  |
| Product description               | With security lock, lock no. 3524 E.  |
| Material                          | Frame: Extruded aluminium sections with die-cast corner pieces<br>Glass panel: Smoked acrylic |
| Supply includes                   | Hinges and assembly parts.<br>Lock insert no. 3524 E  |
| Protection category to IEC 60 529 | IP 54   |
| Dimensions                        | Width: 534 mm<br>Height: 425 mm<br>Depth: 47.5 mm   |
| Visible area                      | Viewing window width: 494 mm<br>Viewing window height: 404.5 mm                               |
| Build depth for components (max.) | 43 mm   |
| Installation dimensions           | Installation depth for components: 482.6 mm<br>Installation width for components: 19"         |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 2.475 kg  |
| Gross weight                      | 2.675 kg  |
| Customs tariff number             | 39205100  |
| ETIM 9                            | EC002527  |
| ETIM 8                            | EC002527  |
| ECLASS 8.0                        | 27182301  |
| Product description               | FT Acrylic glazed cover, 482.6 mm (19"), WHD: 534x425x47,5 mm                                 |