

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2899.320

## Stepped collar

State: 02/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2899.320 - Stepped collar For wall thicknesses from 1.5 to 4.5 mm

For cable entry, simply cut off at the required level to match the cable diameter.



## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SZ 2899.320  |
| Product description                 | For cable entry, simply cut off at the required level to match the cable diameter. |
| Applications                        | For wall thicknesses from 1.5 to 4.5 mm  |
| Material                            | Cover: Thermoplastic elastomer   |
| Dimensions                          | Thread: M32  |
| For wall thickness (max.)           | 1.5 - 4.5 mm   |
| IP protection category to IEC 60529 | IP 54 with careful cable entry   |
| For cable diameters                 | 13 - 26.5 mm   |
| Packs of                            | 25 pc(s).  |
| Net weight                          | 0.1 kg   |
| Gross weight                        | 0.144 kg   |
| Customs tariff number               | 39269097   |
| ETIM 9                              | EC000879   |
| ETIM 8                              | EC000879   |
| ECLASS 8.0                          | 27069216   |

# Features

---

Product description

SZ Stepped collar, for wall thickness from 1,5 bis 4,5 mm, for hole M32, Sealing range: 13-26.5 mm