

# Rittal – The System.

Faster – better – everywhere.



## SV 3055.000 Busbar support

State: 30/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3055.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



## Features

|                       |   |
|-----------------------|---|
| Model No.             | SV 3055.000   |
| Material              | Fibreglass-reinforced, thermoplastic polyester (PBT)<br>Fire protection corresponding to UL 94-V0 |
| Colour                | RAL 7035  |
| Number of poles       | 3-pole<br>150 mm  |
| To fit busbars        | 60 x 10<br>80 x 10  |
| Rated current max.    | 2,500 A   |
| Dimensions            | Width: 30 mm<br>Height: 420 mm<br>Depth: 160 mm   |
| Packs of              | 2 pc(s).  |
| Net weight            | 4.16 kg   |
| Gross weight          | 4.503 kg  |
| Customs tariff number | 85469010  |
| ETIM 9                | EC001166  |
| ETIM 8                | EC001166  |
| ECLASS 8.0            | 27400607  |

# Features

---

|                     |   |
|---------------------|---|
| Product description | SV Busbar support, 3-pole, 150 mm bar centre distance, for busbar<br>WH: 80x10 mm |
|---------------------|---|

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|

# Tender text

SV busbar support  
for accommodating busbars. Suitable for busbars  
up to 3 x 2 x 80 x 10 mm with inserts.

Rated operating voltage: 1000 V~, 50/60 Hz  
to VDE 0660

Rated current: up to 2500 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 150 mm

Tightening torques

Assembly screw: 8 - 10 Nm

Lid attachment: 5 - 10 Nm