

# Rittal – The System.

Faster – better – everywhere.



## SK 3164.115

### Roof-mounted fans

State: 13/03/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.115 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).



## Features

|                                     |                                                                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                           | SK 3164.115                                                                                                                          |
| Benefits                            | Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs<br>Fully wired ready for connection            |
| Material                            | Sheet steel, spray-finished                                                                                                          |
| Colour                              | RAL 7035                                                                                                                             |
| Supply includes                     | Roof-mounted fans<br>Assembly parts                                                                                                  |
| Rated operating voltage             | 115 V, 1~, 50 Hz/60 Hz<br>110 V (DC)                                                                                                 |
| Rated current max.                  | At 50 Hz: 0.6 A<br>At 60 Hz: 0.7 A                                                                                                   |
| Dimensions                          | Width: 511 mm<br>Height: 227 mm<br>Depth: 511 mm                                                                                     |
| IP protection category to IEC 60529 | Internal circuit IP 54                                                                                                               |
| Note                                | Reduction in the specified air throughput to 800 m <sup>3</sup> /h at 40 Pa counterpressure using two vented base/plinth trim panels |
| Operating temperature range         | 20 °C...55 °C                                                                                                                        |

# Features

|                       |           |
|-----------------------|-----------|
| Packs of              | 1 pc(s).  |
| Net weight            | 18.445 kg |
| Gross weight          | 19.416 kg |
| Customs tariff number | 84145915  |
| ETIM 9                | EC000320  |
| ETIM 8                | EC000320  |
| ECLASS 8.0            | 27180716  |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Certificates | EAC                                                       |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |