

Rittal – The System.

Faster – better – everywhere.



SK 3169.007

Roof-mounted fan, roof vent

State: 28/06/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3169.007 - Roof-mounted fan, roof vent

May be installed in any sufficiently large roof surface, air throughput 360 m³/h.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3169.007 |
| Design | Unit ready for connection with built-in radial fan |
| Product modification | Mounting cut-outs are not compatible. If reusing the roof plate, adaptor frame 5050.700 is required. |
| Material | Sheet steel, spray-finished |
| Colour | RAL 7035 |
| Supply includes | Sealing and assembly parts Drilling template Connection cable (3 m) |
| Rated operating voltage | 115 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 65 W |
| Rated current max. | At 50 Hz: 0.55 A |
| Dimensions | Width: 420 mm Height: 95 mm Depth: 340 mm |
| Mounting cut-out | Cut-out width: 345 mm Cut-out depth: 265 mm |
| IP protection category to IEC 60529 | IP 43 |
| Note | Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007 |
| Operating temperature range | -10 °C...60 °C |
| Noise level | At 50 Hz: 53 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 5.828 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 6.135 |
| Customs tariff number | 84145915 |
| EAN | 4028177165359 |
| ECLASS 8.0 | 27180716 |