

# Rittal – The System.

Faster – better – everywhere.



## SK 3244.810 Blue e+ filter fan

State: 19/08/2025 (Source: [rittal.com/uae-en](https://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3244.810 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 – 900 m<sup>3</sup>/h



## Features

|  |   |
|--|---|
| Model No.  | SK 3244.810   |
| Design   | wall-mounted<br>EMC   |
| Product description  | EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.   |
| Benefits   | Easy filter changes, thanks to a new opening mechanism on the louvred grille<br>Faster installation on the enclosure with optimised detent hooks<br>Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability<br>Tool-free assembly |
| Material   | Plastic   |
| Colour   | RAL 7035  |
| Supply includes  | Complete unit ready to install, including EMC filter mat  |
| Fan  | Diagonal, 1~ capacitor motor  |
| Air throughput, unimpeded airflow<br>(with chopped-fibre filter) | At 50 Hz: 700 m <sup>3</sup> /h<br>At 60 Hz: 770 m <sup>3</sup> /h  |

# Features

|   |  |
|---|--|
| Air throughput with matching outlet filter including chopped-fibre filter | At 50 Hz: 537 m³/h<br>At 60 Hz: 587 m³/h   |
| Rated operating voltage   | 115 V, 1~, 50 Hz/60 Hz   |
| Power consumption Pel   | At 50 Hz: 120.7 W<br>At 60 Hz: 166.1 W   |
| Rated current max.  | At 50 Hz: 1.06 A<br>At 60 Hz: 1.47 A   |
| Dimensions  | Width: 323 mm<br>Height: 323 mm<br>Depth: 156 mm   |
| Installation depth  | 136 mm   |
| Mounting cut-out  | Cut-out width: 292 mm<br>Cut-out height: 292 mm  |
| IP protection category to IEC 60 529                                      | IP 54 with chopped-fibre filter<br>IP 56 with chopped-fibre filter and hose-proof hood   |
| Protection category NEMA  | Type 12 with chopped-fibre filter<br>Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood                                 |
| Pre-fuse  | Miniature circuit-breaker/fuse: 6 A  |
| Note  | To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| Operating temperature range   | -30 °C...55 °C   |
| Storage temperature range   | -30 °C...70 °C   |
| Noise level   | At 50 Hz: 64 dB(A)<br>At 60 Hz: 66 dB(A)   |
| Packs of  | 1 pc(s).   |
| Net weight  | 3.84   |
| Customs tariff number   | 84145915   |
| EAN   | 4028177997851  |
| ETIM 9  | EC000320   |

# Features

|            |          |
|------------|----------|
| ETIM 8     | EC000320 |
| ECLASS 8.0 | 27180716 |

# Approvals

|              |  |
|--------------|--|
| Approvals    | CSA<br>30 - KC Korea<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity  |