

# Rittal – The System.

Faster – better – everywhere.



## SK 3340.230

## Rack-mounted fans for 482.6 mm (19")

State: 28/08/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3340.230 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m<sup>3</sup>/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

## Features

|                                     |                                                                                                                                                                                          |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                           | SK 3340.230                                                                                                                                                                              |
| Product description                 | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Colour                              | RAL 7035                                                                                                                                                                                 |
| Supply includes                     | Fully wired unit ready for connection<br>Terminal strip and assembly parts                                                                                                               |
| Air throughput (unimpeded air flow) | 320 m <sup>3</sup> /h                                                                                                                                                                    |
| Rated operating voltage             | 230 V, 1~, 50 Hz/60 Hz                                                                                                                                                                   |
| Rated current max.                  | At 50 Hz: 0.24 A<br>At 60 Hz: 0.22 A                                                                                                                                                     |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 6 A                                                                                                                                                      |
| Dimensions                          | Width: 482.6 mm<br>Height: 44 mm<br>Depth: 200 mm                                                                                                                                        |
| Distance between axes of fans       | 85 mm                                                                                                                                                                                    |
| No. of fans                         | 2                                                                                                                                                                                        |
| Noise level                         | At 50 Hz: 51 dB(A)                                                                                                                                                                       |
| Operating temperature range         | -10 °C...55 °C                                                                                                                                                                           |
| Packs of                            | 1 pc(s).                                                                                                                                                                                 |
| Net weight                          | 2.04                                                                                                                                                                                     |
| Gross weight                        | 2.2                                                                                                                                                                                      |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 84145915      |
| EAN                   | 4028177041448 |
| ETIM 9                | EC000320      |
| ETIM 8                | EC000320      |
| ECLASS 8.0            | 27180716      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Approvals    | UR + C-UR (recognized)<br>VDE                             |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |