



Rittal – The System.

Faster – better – everywhere.



SV 3455.500

Conductor connection clamp

State: 14/02/2026 (Source: rittal.com/uae-en)



SV 3455.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3455.500
Product description	For connecting round conductors and laminated copper bars.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Note	Wire end ferrules should be used with fine wire conductors
Connection of round conductors	1 - 4 mm ²
For bar thickness	10 mm
Packs of	15 pc(s).
Net weight	0.285
Gross weight	0.303
PCF per pack (cradle-to-gate)	1.1 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177042735
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

Tender text

SV conductor connection clamps
for E-CU busbars and Rittal PLS.

For bar thickness: 10 mm

Connection of round conductors: 1 - 4 mm²

Wire end ferrules should be used with
fine wire conductors

Tightening torque

Conductor connection clamp: 2 Nm

Material: sheet steel, zinc plated, passivated