

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.240 Levelling feet HD

State: 08/07/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.240 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | HD 4000.240  |
| Design                | without base mount   |
| Benefits              | Minimises cleaning time thanks to fully covered, permanently sealed threads<br>Compensation of floor inclines up to an angle of 10° thanks to flexible base<br>Baying can even be achieved on sloping floors, thanks to a large levelling range<br>Certification to 3-A Sanitary Standards |
| Material              | Stainless steel 1.4301 (AISI 304)  |
| Supply includes       | Assembly parts and seals   |
| Load capacity         | Max. 7000 N static per levelling foot  |
| Dimensions            | Thread: M12  |
| To fit                | Enclosure type: HD compact enclosure<br>VX<br>VX SE<br>TS  |
| Levelling range       | 122 - 175 mm   |
| Packs of              | 4 pc(s).   |
| Net weight            | 2 kg   |
| Gross weight          | 2.342 kg   |
| Customs tariff number | 73181900   |
| ETIM 9                | EC002622   |
| ETIM 8                | EC002622   |
| ECLASS 8.0            | 27189263   |

# Features

---

Product description

HD Levelling foot, without base mount, Stainless steel 1.4301