

Rittal – The System.

Faster – better – everywhere.



AS 4051.105 LED work light

State: 05/04/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.105 - LED work light for WS 540

For attaching to the table top, with clamping device.



Features

| | |
|----------------------------|--|
| Model No. | AS 4051.105 |
| Product description | For attaching to the table top, with clamping device. |
| Benefits | Bright, glare- and flicker-free lighting, homogeneous and shadow-free Selectable colour temperature between warm white, neutral white and daylight white promotes concentration and reduces symptoms of fatigue Excellent colour fidelity and high contrast Aluminium spring arm with 3D head joint, swivelling and lockable for free positioning of the light source |
| Technical specifications | Spring arm: Length 970 mm Colour reproduction: 94 – 98 Ra Transmission angle: 100° |
| Material | Light housing: Aluminium Glare control: Macrolon |
| Supply includes | LED work light Assembly parts |
| Power consumption | 26 W |
| Length of connection cable | 3 m |
| Connection options | Plug-in power supply (CEE 7/16) with AC adaptor |
| Light | 84 SMD LEDs |

Features

| | |
|-----------------------------|--|
| Protection class | III (SELV) |
| Luminous flux | 2,930 lm |
| To fit Model No. | 4051.100 |
| Operating temperature range | -10 °C...40 °C |
| Rated operating voltage | 110 V - 240 V, 1~, 50 Hz/60 Hz |
| Dimensions | Width: 545 mm Height: 90 mm Depth: 35 mm |
| Packs of | 1 pc(s). |
| Net weight | 2.5 kg |
| Gross weight | 4.2 kg |
| Customs tariff number | 94054990 |
| ETIM 9 | EC002778 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 36629090 |
| Product description | LED work light for WS 540, dimmable, 230 V/50 Hz |