

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.003 Crimping pliers

State: 27/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.003 - Crimping pliers for wire end ferrules

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4054.003  |
| Design                   | Straight   |
| Product description      | For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4. |
| Benefits                 | Minimal effort required with large wire cross-sections<br>Uniformly high quality compression<br>Releasable ratchet<br>Self-adjusting             |
| Material                 | High-quality special tool steel  |
| Surface finish           | Matt, plated   |
| Colour                   | Handle: Anthracite and Rittal Power Pink   |
| Compression              | Hexagonal crimp  |
| Direction of cable entry | Side   |
| Dimensions               | Length: 176 mm   |
| AWG                      | 26 - 8   |
| For cross-section        | 0.14 - 10 mm <sup>2</sup>  |
| Packs of                 | 1 pc(s).   |
| Net weight               | 0.4 kg   |
| Gross weight             | 0.455 kg   |
| Customs tariff number    | 82032000   |
| ETIM 9                   | EC000168   |
| ETIM 8                   | EC000168   |

# Features

---

ECLASS 8.0

21043811

---

Product description

AS crimping tool, hexagon, for cross-section 0.14 – 10 mm<sup>2</sup>