

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.023 Crimping pliers

State: 17/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.023 - Crimping pliers for ring terminals

For use with non-insulated ring terminals



## Features

|                       |   |
|-----------------------|---|
| Model No.             | AS 4054.023   |
| Design                | Straight  |
| Product description   | For use with non-insulated ring terminals.  |
| Benefits              | Releasable ratchet<br>Optimised lever transmission means that only minimal actuator forces are required, even with large cross-sections |
| Material              | High-quality special tool steel   |
| Surface finish        | Matt, plated  |
| Colour                | Handle: Anthracite and Rittal Power Pink  |
| Compression           | Double-indent crimp   |
| Dimensions            | Height: 68 mm<br>Length: 256 mm   |
| AWG                   | 12 - 8  |
| For cross-section     | 4 - 10 mm <sup>2</sup>  |
| Packs of              | 1 pc(s).  |
| Net weight            | 0.63 kg   |
| Gross weight          | 0.668 kg  |
| Customs tariff number | 82032000  |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 9              | EC000168   |
| ETIM 8              | EC000168   |
| ECLASS 8.0          | 21043811   |
| Product description | Crimping plier 4 - 10 mm <sup>2</sup> , d-indent |

---