

Rittal – The System.

Faster – better – everywhere.



SZ 4127.010 Door-operated switch

State: 05/08/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4127.010 - Door-operated switch

with mounting accessories, with or without connection cable.

Features

| | |
|---|--|
| Model No. | SZ 4127.010 |
| Design | Without connection cable |
| Note | For installation in VX IT only in conjunction with VX mounting bracket for door-operated switch |
| Rated impulse withstand voltage, phase to phase | 6000 V AC |
| Rated insulation voltage | 400 V AC |
| Installation options | for LED system light for standard and courtesy light without integral door-operated switch for cooling units and air-water heat exchangers |
| Electrical connection | 240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A |
| Rated operating voltage | 400 V |
| IP protection category to IEC 60 529 | IP 40 |
| Packs of | 1 pc(s). |
| Net weight | 0.068 |
| Gross weight | 0.076 |
| Customs tariff number | 85365019 |
| EAN | 4028177497740 |
| E-Number Sweden | E3404494 |
| ETIM 9 | EC002626 |
| ETIM 8 | EC002626 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27189266 |
|------------|----------|

Approvals

| | |
|--------------|---|
| Approvals | CQC CQC-CCC CSA UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
