

Rittal – The System.

Faster – better – everywhere.



SZ 4139.150 Courtesy light

State: 04/06/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4139.150 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

Features

| | |
|--|---|
| Model No. | SZ 4139.150 |
| Design | with door-operated switch |
| Supply includes | Courtesy light Light Light cover Assembly parts Integral door-operated switch |
| Power consumption | 14 W |
| Ballast | Wide-range electronic ballast |
| Connection options | Power supply via connectors Through-wiring (creating rows of lights) |
| Integral door-operated switch | Yes |
| Light | Fluorescent lamp, base G13 |
| Protection class | I (PE conductor) |
| Switch (type) | Integral on/off/door-operated switch |
| Light cover | Yes |
| Light – installation type | Screw-fastening |
| Rated impulse withstand voltage, phase to earth | 1000 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |

Features

| | |
|-----------------------------|--|
| Installation options | TS horizontal section of the roof frame: direct TS, SE vertical section: with TS adaptor bracket SE sections at the front and rear of the roof frame: with TS adaptor bracket SE extrusions at the side of the roof frame: direct |
| Dimensions | Width: 452 mm Height: 117 mm Depth: 50 mm |
| Operating temperature range | -15 °C...45 °C |
| Sockets | D, earthing-pin (type F, CEE 7/4) |
| Storage temperature range | -20 °C...70 °C |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Socket version | D, earthing-pin (type F, CEE 7/4) |
| Packs of | 1 pc(s). |
| Net weight | 1.25 kg |
| Gross weight | 1.319 kg |
| Customs tariff number | 94054990 |
| ECLASS 8.0 | 27189241 |
| Product description | SZ Courtesy light, WHD: 452x117x50 mm, 14 W, 100-240 V, 50/60 Hz, with door-operated switch, with earthing-pin socket |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|
