


# Rittal – The System.

Faster – better – everywhere.



## SZ 4315.520

### Door-operated switch

State: 15/05/2024 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4315.520 - Door-operated switch

with mounting accessories, with or without connection cable.

## Features

Model No.	SZ 4315.520
Design	With connection cable
Length	600 mm
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for standard and courtesy light without integral door-operated switch
Dimensions	Length: 600 mm
Electrical connection	240 V AC/6 A 125 V AC/8 A 24 V AC/6 A 24 V DC/6 A
Rated operating voltage	400 V
IP protection category to IEC 60529	IP 40
Packs of	1 pc(s).
Weight/pack	0.12 kg
Customs tariff number	85365080
EAN	4028177581357
ETIM 7.0	EC002626
ECLASS 8.0	27189266

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK