

**Rittal – The System.**

Faster – better – everywhere.



**VX 5301.337**

**Gland plate set, multi-piece, solid**

State: 08/07/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.337 - Gland plate set, multi-piece, solid for VX IT

Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry.

## Features

|                               |  |
|-------------------------------|--|
| Model No.                     | VX 5301.337  |
| Product description           | Multi-piece gland plate set consisting of solid base plate modules and a sliding panel for cable entry. The solid gland plate module, depth 237.5 mm, may optionally be exchanged for gland plate module variants for cable entry. |
| Benefits                      | The sequence of individual modules may be freely selected  |
| Material                      | Sheet steel  |
| Surface finish                | Zinc-plated  |
| Supply includes               | Gland plate set<br>Sealing tape<br>Assembly parts<br>1 gland plate module, solid, depth: 75 mm<br>2 gland plate modules, solid, depth: 237.5 mm<br>1 sliding panel, depth: 115 mm  |
| To fit                        | Enclosure type: VX IT<br>Width: = 800 mm<br>Depth: = 800 mm  |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 6.42 kg  |
| Gross weight                  | 6.44 kg  |
| PCF per pack (cradle-to-gate) | 24.1 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared   |
| Customs tariff number         | 94039910   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |

# Features

---

Product description

VX IT gland plate module, multi-piece, solid, for width 800 mm, W x D 800 x 800 mm, sheet steel