


Rittal – The System.

Faster – better – everywhere.



VX 5301.423

Glazed aluminium door, one-piece

State: 13/05/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.423 - Glazed aluminium door, one-piece for VX IT

To replace existing doors.



Features

| | |
|----------------------|---|
| Model No. | VX 5301.423 |
| Product description | To replace existing doors. |
| Material | Frame: Extruded aluminium section Vertical extrusion: Aluminium, anodised Horizontal extrusion: Aluminium, spray finished Viewing window: Single-pane safety glass, 3 mm |
| Colour | Comfort handle VX, hinges, horizontal extrusion: RAL 9005 Vertical profile: silver coloured |
| Supply includes | Door with comfort handle VX for semi-cylinders with security lock 3524 E 3 x 180° hinges, fitted Assembly parts |
| Assembly instruction | For a door opening angle of 180° when baying, a 180° baying hinge is required |
| Note | Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 105° |

Features

| | |
|-------------------------------------|---|
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 16.142 kg |
| Gross weight | 17.2 kg |
| PCF per pack (cradle-to-gate) | 65.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |
| Product description | Aluminium glazed door, one-piece for VX IT, to replace existing doors. For enclosure width 800 mm, for enclosure height 2,000 mm, frame: extruded aluminium section |